

Anycubic Photon Mono M5s Resin 3D Printer

Level 3

Features


- Maximum print size: 7.87" H x 8.58" W x 4.84" D (200x218x123mm HWD)
- Anycubic Photon Workshop slicing software
- USB drive to import prints
- Wash station
- UV Curing Station

What You'll Need

- STL, OBJ, 3MF, IGES, or STEP file saved to USB drive.
- A computer is required to print.
- During the learning phase a limited supply of gray high-speed resin is available for use.

Please Note

- Must wear gloves, a dust mask, safety glasses, and protective clothing that covers exposed skin.
- Prints cannot run overnight.
- Once the print is finished, you will need to work with a staff member to get it off the platform and into the wash and cure station to clean it.
- All resin must be cured.
- Do not throw away anything that has not been cured.



*Once you've moved from learning to production, printing fees may apply. Ask staff for information.